TOSHIBA

©-STUDIO™8518A series

- > Black & White Multifunction Printer
- > Up to 85 PPM
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP



C-STUDIO 5518A/6518A/7518A/8518A

Main Specifications

Copy System Indirect Electrostatic Photographic Method/ /Laser Printing/

Heat Roller Fusing

Display 10.1" Color WSVGA Touch Screen Tilting Display

Copy Speed First Copy Out 55/65/75/85 PPM (LT) 5.2/5.2/4.5/4.1 Seconds Warm-Up Time Approx. 24/24/20/20 Seconds

Copy Resolution 2400 dpi (Equivalence) x 600 dpi (with Smoothing) Stack Feed Bypass 3.9" x 5.8" to 13" x 19", 12" x 47" Banner, Envelope

Multiple Copying Up to 9,999 Copies

Paper Capacity Standard 3,520 Sheets/Max. 6,020 Sheets (Tandem Drawer)

Original Feed Standard 300-Sheet DSDF

DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), Scan Speed & Weights

Simplex: 9.3-110 lb Index, Duplex: 9.3-110 lb Index

Max. Original Size

Duplex

Drawers: 540 Sheets-ST-R to 12" x 18" Paper Feed Sizes Integral Tandem LCF 1,160 x 2 LT-Only

Stack Feed Bypass: 120 Sheets-3.9" x 5.8" to 13" x 19", 12" x 47" Banner

Opt. 2,500-Sheet Ext. LCF LT-Only Tandem LCF 1,160 Sheets x 2-16 lb Bond-140 lb Index

Paper Weights Plus 540 Sheets x 2-16 lb Bond-140 lb Index

Stack Feed Bypass: 120 Sheets-16 lb Bond-110 lb Cover Opt. 2,500-Sheet Ext. LCF LT-Only-16 lb Bond-140 lb Index Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)

Reproduction Ratio 25% to 400% Max. 520K/590K/660K/720K Month

Max Duty Cycle Approx.430 lb Weight

37.6" (W) x 27.5" (D) x 48.3" (H) Approx. Dimensions

Toner Yield 106,600 @ 5%

Power Source 120 Volts, 50/60 Hz, 16 Amps **Power Consumption** Maximum 2.0kW (120V) CPU Intel Atom™ 1.33 GHz (Dual-Core)

Memory

320GB Self-Encrypting Drive **Hard Disk Drive**

e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, NFC Authentication

Conformance with HCD-PPv1.0 in High Security Mode.

Environmental Stds. Certification

ENERGY STAR® (V3.0), EPEAT Gold WHQL (Windows® 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell®, Citrix®, SAP,

AirPrint®, Mopria®

Scan Specifications

Scan Speed Scan Modes Scan Resolution File Formats

DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color) Standard: Full Color, Auto Color, Monochrome, Grayscale

600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi

Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX

(Opt.), PPTX (Opt.) Color/Grayscale: JPEG (High, Middle, Low) Image Compression

Facsimile Specifications

Compatibility **Data Compression** MH/MR/MMR/JBIG Approx. 3 Seconds Per Page Transmission Speed Up to 33.6 Kbps Fax Modem Speed

Memory Transmission 100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job

0.7 Seconds Per Page, Maximum 73 IPM Scan Speed

e-BRIDGE Next Print Specifications

PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG

Print Speed

55/65/75/85 PPM (LT) 600 x 600 dpi, 2,400 (Equivalence) x 600 dpi (With Smoothing), 1,200 x 1,200 Print Resolution

dpi (2-bit) or 3,600 (Equivalence) x 1,200 dpi, PS Only

Windows® 8.1,10, Windows Server® 2012/R2, Windows Server 2016® **Operating Systems** Macintosh® (macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13,

11.4), Unix®, Linux®

TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, **Network Protocols**

EtherTalk for Macintosh® Environments

SMB, LPR/LPD, IPP (Ver.2.0) w/Authentication, AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/iPrint, WS Print, FTP **Printing Protocols**

Print Drivers Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server 2016°, Windows° 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13, 11.4

RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional Interface

802.11b/g/n, Wireless LAN, Optional Bluetooth

AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play) Wireless Device

TopAccess, EFMS 6.3 (e-BRIDGE Fleet Management Software) **Device Management**

Account Control Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function

Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen **Accessibility Features**

Timeout and Audible Beep Message Alerts User Authentication, On-Board Data Scramble Function. SCEP. Disable **Security Features**

e-Filing Specifications

Operation Method **Number of Boxes** Capacity of Boxes

Color Touch Screen Control Panel or Client PC 1 Public Box, 200 Private User Boxes 100 Folders Per Box, 400 Documents Per Folder/Box,

200 Pages Per Document

Accessories (Options)

Additional Paper Options Large Capacity Feeder	MP2502B
Finishing Options	
50-Sheet Staple Finisher	MJ1111B
Saddle-Stitch Finisher	MJ1112B
Hole Punch Unit for MJ1111B/MJ1112B	MJ6106N
Side Exit Tray	KA6551
Finisher Guide Rail	KN1103
Connectivity/Security Options	00407011

Connectivity/Security Options	
FAX Unit/2nd Line for FAX Unit	GD1370N
Wireless LAN/Bluetooth	GN4020
Bluetooth Keyboard	GR9000
Accessory Tray	GR1330
Panel 10-Key Option	GR1340
Card Reader Holder	GR1320
Meta Scan Enabler	GS1010

GP1080
GS1007
GE1230
GS1080NODE
GS1090NODE
GB2300NODE
GB2310NODE
GB2320NODE

Accessible Arm KK2550 Harness Kit for Coin Controller GQ1280 Manual Pocket KK5008

















Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Tone yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries

Corporate Office

East Coast

Midwest

South

West Coast

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000 2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385

Tel: 949-462-6000

Tel: 973-316-2700

25530 Commercentre Drive, Lake Forest, CA 92630

959 Route 46 East, 5th Floor, Parsippany, NJ 07054

25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000 Web Site www.business.toshiba.com