

# TOSHIBA PRINTER AND PANTHER SHADOW PRINT & APPLY SYSTEM

- > Entry Level Print and Apply System
- > Toshiba BEX4T1 or BEX4T2 Industrial printers
- > Prints and applies label up to 4.7" x 8"
- > Applies 10-40 labels per minute\*
- > 800 meter/2,624' – 8"OD Ribbon (BEX4T1)
- > Stand-Alone or automated production integration



\*Varies depending on label length, printer speed, and height of the product labeled.

**TOSHIBA**

# TOSHIBA PRINTER AND PANTHER SHADOW PRINT & APPLY SYSTEM

- Entry Level Print and Apply System
- Toshiba BEX4T1 or BEX4T2 Industrial printers
- Prints and applies label up to 4.7" x 8"
- Applies 10-40 labels per minute\*
- 800 meter/2,624' – 8'OD Ribbon (BEX4T1)
- Stand-Alone or automated production integration



\*Varies depending on label length, printer speed, and height of the product labeled.

**STANDARD FEATURES**



**Printer**

- > Rugged Industrial printer series
- > BEX4T1 or BEX4T2 printer
- > Thermal Transfer or Direct Thermal printers
- > Resolution in 200 or 300 DPI
- > Maximum print speed – 14 IPS (BEX4T1)  
12 IPS (BEX4T2)
- > Label Roll 8” OD, 3” Roll Core
- > Large Ribbon Capacity  
800 meter (BEX4T1)  
600 meter (BEX4T2)
- > Label Roll 8” OD, 3” Roll Core

- > Long head life warranty –  
3 million linear inches
- > Programming language –  
TPCL (Toshiba), ZPL (Zebra)
- > Printer Communication Interface –  
USB and Ethernet

**Applicator**

- > 13” Stroke (Peel/Home to base +13”)
- > Auto – Tamp Product Contact Sensing
- > Print Request Push Button
- > Table Top mount

**OPTIONAL STAND**




Top Apply-Optional Stand



Side Apply-Optional Stand

Models	PASHADOWT1	PASHADOWT2
<b>Printer Specification</b>		
Printer Model	BEX4T1GS12DM01	BEX4T2GS12M01
Head Type	New Edge	Flat
Technology	Thermal Transfer/Direct Thermal	Thermal Transfer/Direct Thermal
Resolution	203 or 305 DPI	200 or 300 DPI
Print Speed	14 IPS	12 IPS
Print Width (Max)	4.09”	4.09”
<b>Media</b>		
Ribbon Length (Max)	800M (2,624’)	600M (1,968’)
Ribbon Core Diameter	1”	1”
Ribbon Outer Diameter (OD)	3.45”	3.45”
Ribbon Type	CSO	CSO
Label Width (Min-Max)	.98” – 4.72”	.98” – 4.72”
Label Length (Min-Max)	2” – 8”	2” – 8”
Label Core Diameter	3”	3”
Label Outer Diameter (OD)	8” Roll	8” Roll
<b>Printer Communication (Std)</b>	USB, Ethernet	USB, Ethernet
<b>Printer Communication (Opt)</b>	USB, Ethernet, Serial USB, Ethernet, Parallel USB, Ethernet, Wireless (802.11 b/g)	USB, Ethernet, Serial USB, Ethernet, Parallel USB, Ethernet, Wireless (802.11 b/g)
Options	RFID, Ribbon Save	
<b>Printer Environment</b>		
Operating Temperature	40 °- 104° F (5° to 40°C)	40 °- 104° F (5° to 40°C)
Humidity	25-85% RH (Non-Condensing)	25-85% RH (Non-Condensing)
<b>Shadow Applicator (standard)</b>		
Type	Electric – No Compressed Air	Electric – No Compressed Air
Stroke	13” (Peel/Home to Base +13”)	13” (Peel/Home to Base +13”)
Tamp	Auto-Tamp Product Contact Sensing Print Request Push Button	Auto-Tamp Product Contact Sensing Print Request Push Button
Power	Electrical 115-240 VAC, 50/60 Hz at 5A max (No Air Required)	Electrical 115-240 VAC, 50/60 Hz at 5A max (No Air Required)
Configuration	Table - Top	Table - Top
<b>Applicator (option)</b>	Stand Mount – Side Apply Stand Mount – Top Apply Palm Switch Foot Switch	Stand Mount – Side Apply Stand Mount – Top Apply Palm Switch Foot Switch
<b>Applicator Shipping Weight</b>	97 LBS	97 LBS


**SPECIFICATIONS**



Side View



Front View



Top View



Scan for more info

