TOSHIBA



C-STUDIO 2525AC/3025AC/3525AC/4525AC

MAIN SPECIFICATIONS

Copy System Indirect Electrostatic Photographic/OPC/Laser Printing/Heat Roller Fusing 10.1" Color WSVGA Touch Screen Tilting Display 25/30/35/45 PPM (LT)

Copy Speed First Copy Out

Color: Less Than 7.8/7.8/7.8/5.7 Seconds Monochrome: Less Than 5.9/5.9/5.9/4.4 Seconds Warm-Up Time From powering on: Approx. 20 Seconds From Sleen & Low Power: Less Than 12 Seconds

Copy Resolution 600 x 600 dpi

Stack Feed Bypass 3.9" x 5.8" to 12" x 18", 12" x 47" Banner, Envelope Multiple Copying Up to 999 Copies Standard 1,200 Sheets/Max. 5,200 Sheets

Paper Capacity Original Feed 300-Sheet DSDF or DSDF with Double Feed Detection or 100-Sheet RADF

Scan Speed & Weights DSDF Scan: 70IPM (Monochrome or Color), Simplex or Duplex: 9.3-110lb Bond RADF Scan: 50IPM (Monochrome or Color), Simplex: 9.3-41.8lb Bond, Duplex: 13.3-41.8lb Bond

Max. Original Size

Drawer 1: 550 Sheets-ST-R to LD Paper Feed Sizes Drawer 2: 550 Sheets-ST-R to 12" x 18'

Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 12" x 18", 12" x 47" Banner

Opt. 550-Sheet Paper Feed Pedestal-ST-R to 12" x 18"

Opt. 550-Sheet Drawer for PFP-ST-R to 12" x 18" Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-

ST-R to LG

Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only Opt. 2,000-Sheet External LCF-LT Only

Standard: 550 Sheets x 2-16lb Bond-110lb Cover Paper Weights Stack Feed Bypass: 100 Sheets-14lb Bond-110lb Cover

Opt. 550-Sheet Paper Feed Pedestal-16lb Bond-110lb Cover Opt. 550 Sheets Drawer for PFP-16lb Bond-110lb Cover Opt. Envelope Cassette for PFP-16lb Bond-140lb Index Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-17lb-28lb Bond Opt. 2,000-Sheet External LCF-LT 16lb Bond-110lb Cover Standard Automatic Duplex Unit (16lb Bond-140lb Index)

25% to 400% Reproduction Ratio

Max. 75K/90K/105K/105K Month (Color: 100%) Max Duty Cycle

Max. 150K/180K/210K/210K Month (Monochrome: 100%)

Approx. 169lb/172lb Weight Approx. Dimensions 23" (W) x 25.2" (D) x 31" (H) CMYK Toner Yield CMY: 38K, K: 39.8K @ 5% 120 Volts, 50/60 Hz, 12 Amps Power Source **Power Consumption** Maximum 1.8kW (120V)

NEMA 5-15 Plug Type 4GR

Memory Hard Disk Drive 128GB Solid State Drive (SSD) Security Features

User Authentication, Trusted Platform Module, On-Board Data Scramble Function, SCEP, Disable, e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS, SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, Biometric Authentication

Environmental Standards Certifications

*Conformance with HCD-PPv1.0 in High Security Mode ENERGY STAR® (V3.1), EPEAT Gold, Californian Proposition 65 WHQL (Windows® 8, 8.1, 10, 11, 2012, 2012 R2, 2016/19/22), Novell®,

Citrix®, SAP, AirPrint® and Mopria®

SCAN SPECIFICATIONS

Scan Speed DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex

(Monochrome or Color) RADF Scan: Up to 73 IPM (Monochrome or Color)

Scan Modes Standard: Full Color, Auto Color, Monochrome, Grayscale

OCR DOC/XLS/PPT/PDF Scan Resolution

600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi **File Formats**

Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, PDF/A, Searchable PDF, XPS-Multi/Single Page, DOCX, XLSX, PPTX, Color/ Grayscale: JPEG, TIFFMulti/Single Page, PDF-Multi/Single Page, PDF/A, Slim PDF, Searchable PDF, XPSMulti/Single Page, DOCX,

Image Compression Color/Grayscale: JPEG (High, Middle, Low)

FACSIMILE SPECIFICATIONS

Compatibility Super G3 Data Compression MH/MR/MMR/JBIG Transmission Speed Approx. 3 Seconds Per Page Fax Modem Speed Up to 33.6 Kbps

100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job Memory Transmission Scan Speed

0.7 Seconds Per Page, Maximum 73 IPM

e-FILING SPECIFICATIONS

Operation Method Number of Boxes Capacity of Boxes

Color Touch Screen Control Panel or Client PC 1 Public Box. 200 Private User Boxes 100 Folders Per Box, 400 Documents Per Folder/Box,

200 Pages Per Document

KD1072

MY1052

MY1053

MP2002

MJ1048

MJ1113

MJ1114

M.16011

MJ6107

KN5005

MJ5015

GD1370N

GN4030A3

GR9001

GR1430

GR1420

GS1100NODE

GS1010NODE

KD1073LT

e-BRIDGE NEXT PRINT SPECIFICATIONS

Print Resolution

Print Drivers

Wireless Device

Interface

PDL

Duplex

600 x 600 dpi (5 bit), 1,200 x 1,200 dpi (Color/2 bit) or 3,600 (Equivalence) x 1,200 dpi (BW/with Smoothing) (PS3 Only)

Windows® 8.1,10, 11, Windows Server® 2012/R2, Windows Server® **Operating Systems** 2016/19/22, Macintosh® (macOS X 10.10-15, 12), Unix®, Linux® TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for NovelI® **Network Protocols** Environments, EtherTalk for Macintosh Environments

SMB V1-3, LPR/LPD, IPP V1.2 w/Authentication (TLS 1.2/1.3), AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/iPrint, Bluetooth (HCRP/BIP/OPP/FTP), WS Print, FTP **Printing Protocols**

PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG

Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server® 2016/19/22, Windows® 10, 11 (64-bit), macOS X 10.12-15, 11, 12

RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional IEEE802.11b/g/n, Wireless LAN, Optional Bluetooth

AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)

Device Management TopAccess Account Control

Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and

User Function

Accessibility Features Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout, Audible Beeps, Optional Voice Assist

Platen & Document Feeder Options

MR4010 DSDF MR4020 DSDF with Double Feed Detection RADF MR3033 Platen Cover KA5005PC

ACCESSORIES (OPTIONS)

Additional Paper Options Paper Feed Pedesta Drawer Module Envelope Cassette Option

Large Capacity Feeder External Large Capacity Feeder **Finishing Options**

50-Sheet Inner Finisher 65-Sheet Staple Finisher 65-Sheet Saddle-Stitch Finisher Hole Punch for MJ1048 Hole Punch for MJ1113/MJ1114 Bridge Kit

Job Separator **Connectivity/Security Options**

Meta Scan Enabler

FAX Unit/2nd Line for FAX Unit Wireless LAN/Bluetooth Fax Over IP License Key Bluetooth Keyboard 2nd NIC Holder USB Hub

IPSec Enabler Unicode Font Enabler Multi-Station Print Enabler Per Seat License

e-BRIDGE Plus for OneDrive for Business V3.0 e-BRIDGE Plus for SharePoint Online V3.0 e-BRIDGE Plus for Exchange

Online V3.0 e-BRIDGE Plus for Gmail e-BRIDGE Plus for Google Workspace Hardcopy Security Printing

Security SSD (512GB) FIPS HDD (320GB)

e-BRIDGE Plus Voice Guidance e-BRIDGE Global Print Miscellaneous Options Card Reader Holder

Accessory Tray Panel 10-Key Option STAND5015 Stand Work Tray Manual Pocket Harness for Coin Controller Accessible Arm

KK5008 GQ1280 KK2560

GP1080NODE

GS1007NODE

GS1090NODE

GB2300NODE

GR2310NODE

GB2320NODE

GB2380NODE

GB2390NODE

GP1190NODE

GB2540NODE

GB2550NODE

GE1280

GF1260

GR1320

GR1330

GR1340

KK5005















Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

East Coast

Midwest

South **West Coast** 25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000 2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385

25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000

Website www.business.toshiba.com