# **TOSHIBA**



## E-STUDIO 5525AC/6525AC

#### MAIN SPECIFICATIONS

Copy System Indirect Electrostatic Photographic/OPC/Laser Printing/Heat Roller Fusing

10.1" Color WSVGA Touch Screen Tilting Display 55/65 PPM (LT)

Copy Speed First Copy Out

Color: Less Than 5.7/5.7 Seconds Monochrome: Less Than 4.3/4.3 Seconds Warm-Up Time From powering on: Approx. 26 Seconds From Sleep & Low Power: Less Than 20 Seconds

**Copy Resolution** 600 x 600 dpi

Stack Feed Bypass 3.9" x 5.8" to 12" x 18", 12" x 47" Banner, Envelope Multiple Copying Up to 999 Copies Standard 1,200 Sheets/Max. 5,200 Sheets

Paper Capacity

Original Feed 300-Sheet DSDF or DSDF with Double Feed Detection or 100-Sheet RADF Scan Speed & Weights DSDF Scan: 70IPM (Monochrome or Color), Simplex or Duplex: 9.3-110lb Bond, RADF Scan: 50IPM (Monochrome or Color), Simplex: 9.3-41.8lb

Bond, Duplex: 13.3-41.8lb Bond

Max. Original Size

Paper Feed Sizes Drawer 1: 550 Sheets-ST-R to LD Drawer 2: 550 Sheets-ST-R to 12.5" x 18

Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 12.5" x 18", 12" x 47" Banner

Opt. 550-Sheet Paper Feed Pedestal-ST-R to 12.5" x 18" Opt. 550-Sheet Drawer for PFP-ST-R to 12.5" x 18" Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-

ST-R to LG

Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only Opt. 2,000-Sheet External LCF-LT Only

Standard: 550 Sheets x 2-16lb Bond-110lb Cover Paper Weights

Stack Feed Bypass: 100 Sheets-14lb Bond-110lb Cover Opt. 550-Sheet Paper Feed Pedestal-16lb Bond-110lb Cover Opt. 550 Sheets Drawer for PFP-16lb Bond-110lb Cover

Opt. Envelope Cassette for PFP-16lb Bond-140lb Index Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-17 lb-28lb Bond Opt. 2,000-Sheet External LCF-LT 16lb Bond-110lb Cover Standard Automatic Duplex Unit (16lb Bond-140lb Index)

25% to 400% Reproduction Ratio

Max Duty Cycle Max. 106K/115K Month (Color: 100%) Max. 212K/230K Month (Monochrome: 100%)

Approx.173lb Weight

Approx. Dimensions

23" (W) x 25.2" (D) x 31" (H) CMY: 38K, K: 39.8K @ 5% 120 Volts, 50/60 Hz, 12 Amps CMYK Toner Yield Power Source **Power Consumption** Maximum 1.8kW (120V)

e-STUDIO5525AC: NEMA 5-15, e-STUDIO6525AC: NEMA 5-20 Plug Type

Memory Hard Disk Drive

128GB Solid State Drive (SSD)

**Security Features** 

User Authentication, Trusted Platform Module, On-Board Data Scramble Function, SCEP, Disable, e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS, SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IECT408)\* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, Biometric Authentication \*Conformance with HCD-PPv1.0 in High Security Mode

**Environmental Standards** 

Image Compression

ENERGY STAR® (V3.1), EPEAT Gold, Californian Proposition 65 Certifications WHQL (Windows® 8, 8.1, 10, 11, 2012, 2012 R2, 2016/19/22), Novell®,

Citrix®, SAP, AirPrint® and Mopria®

#### **SCAN SPECIFICATIONS**

DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex Scan Speed

(Monochrome or Color)

RADF Scan: Up to 73 IPM (Monochrome or Color) Scan Modes Standard: Full Color, Auto Color, Monochrome, Grayscale OCR

DOC/XLS/PPT/PDF Scan Resolution

**File Formats** 

DUC/XLS/PP1/PDF 600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, PDF/A, Searchable PDF, XPS-Multi/Single Page, DOCX, XLSX, PPTX Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, PDF/A, Slim PDF, Searchable PDF, XPS-Multi/Single Page, DOCX, XLSX, PPTX

Color/Grayscale: JPEG (High, Middle, Low)

#### **FACSIMILE SPECIFICATIONS**

Super G3 MH/MR/MMR/JBIG Compatibility **Data Compression** Transmission Speed Approx. 3 Seconds Per Page

Up to 33.6 Kbps Fax Modem Speed

100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job 0.7 Seconds Per Page, Maximum 73 IPM **Memory Transmission** 

Scan Speed

#### e-FILING SPECIFICATIONS

Color Touch Screen Control Panel or Client PC Operation Method 1 Public Box, 200 Private User Boxes Number of Boxes

**Capacity of Boxes** 100 Folders Per Box, 400 Documents Per Folder/Box.

200 Pages Per Document

GD1370N

GR9001 GR1430

GR1420

Tel: 949-462-6000

Tel: 973-316-2700

Tel: 773-380-6000

Tel: 678-546-9385

GN4030A3

GS1100NODE

GS1010NODE

GP1080NODE

### e-BRIDGE NEXT PRINT SPECIFICATIONS

PDL **Print Resolution** 

Duplex

600 x 600 dpi (5 bit), 1,200 x 1,200 dpi (Color/2 bit) or 3,600 (Equivalence) x 1,200 dpi (BW/with Smoothing) (PS3 Only) Windows® 8.1,10, 11, Windows Server® 2012/R2, Windows Server® **Operating Systems** 

**Network Protocols Printing Protocols** 

**Print Drivers** 

Interface

Wireless Device

Account Control

Device Management

PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG

(on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function

**Accessibility Features** 

2016/19/22, Macintosh® (macOS X 10.10-15, 12), Unix®, Linux® TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for NovelI® Environments, EtherTalk for Macintosh Environments SMB V1-3, LPR/LPD, IPP V1.2 w/Authentication (TLS 1.2/1.3), AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/iPrint, Bluetooth (HCRP/BIP/OPP/FTP), WS Print, FTP Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server® 2016/19/22, Windows® 10, 11 (64-bit), macOS X 10.12-15, 11, 12 RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional IEEE802.11b/g/n, Wireless LAN, Optional Bluetooth AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play) TopAccess Up to 10,000 Users or 1,000 Departments Supports User Authentication

Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable







Screen Timeout, Audible Beeps, Optional Voice Assist





#### **ACCESSORIES (OPTIONS)** Platen & Document Feeder Options

MR4010 DSDF DSDF with Double Feed Detection MR4020 RADF MR3033 Platen Cover KA5005PC **Additional Paper Options** Paper Feed Pedest KD1072 Drawer Module MY1052 Envelope Cassette Option MY1053 Large Capacity Feeder KD1073LT External Large Capacity Feeder MP2002 Finishing Options 65-Sheet Staple Finisher MJ1113 65-Sheet Saddle-Stitch Finisher Hole Punch for MJ1113/MJ1114 MJ1114 M.16107 KN5005 Bridae Kit Job Separator MJ5015

Connectivity/Security Options FAX Unit/2nd Line for FAX Unit Wireless LAN/Bluetooth Fax Over IP License Key Bluetooth Keyboard 2<sup>nd</sup> NIC Holder

USB Hub Meta Scan Enabler IPSec Enabler

Unicode Font Enabler GS1007NODE Multi-Station Print Enabler Per Seat License GS1090NODE e-BRIDGE Plus for OneDrive for Business V3.0 GB2300NODE

e-BRIDGE Plus for SharePoint Online V3.0 e-BRIDGE Plus for Exchange GB2310NODE Online V3.0 GB2320NODE e-BRIDGE Plus for Gmail GB2380NODE e-BRIDGE Plus for Google

GB2390NODE Workspace Hardcopy Security Printing GP1190NODE Security SSD (512GB) FIPS HDD (320GB) GE1280 GF1260 e-BRIDGE Plus Voice Guidance GB2540NODE e-BRIDGE Global Print GB2550NODE

**Miscellaneous Options** GR1320 Card Reader Holder GR1330 Accessory Tray Panel 10-Key Option GR1340 Stand STAND5015 Work Tray KK5005 Manual Pocket KK5008 Harness for Coin Controller GQ1280 Accessible Arm KK2560









Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies

time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective

manufactured or designated by Toshiba. Not all options and accessories may be available at the



**Corporate Office** 

**East Coast** 

Midwest

South

Website

West Coast

25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000

2037 Bakers Mill Rd., Dacula, GA 30019

25530 Commercentre Drive, Lake Forest, CA 92630

959 Route 46 East, 5th Floor, Parsippany, NJ 07054

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

www.business.toshiba.com

companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries. © 2022 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code 22414 5525AC/6525AC Spec Sheet 5K PG 6/22