



Document
Workflow
Solution

- > Select
- > **Scan**
- > Send
- > Store
- > Search
- > Secure

Scan to Word®, PDF & 19 other file formats ...create your own digital library



The common filing cabinet not only takes up costly floor space it also poses obvious security and environmental risks. Add to that the number of valuable employee hours lost sorting, storing and searching for documents and you have a considerable workflow challenge.

Toshiba's e-BRIDGE Re-Rite™ is the ideal solution. It transforms paper documents into editable digital libraries instantly. What's more, it's so easy the whole office can use it.

Virtually no training is required. The MFP user interface is so simple to use because all processing is done in a totally hands-off operation.

SELECT and convert to 21 editable file formats including Microsoft® Word® and Excel®, Adobe® PDF and more.

SCAN from a single page to many. RE-RITE® and Toshiba MFPs offer a host of simple solutions including batch scanning with barcode separation, page splitting, blank page removal, job preview and automatic page orientation.

SEND converted documents with ease, directly to network drives, via ftp or by secure email and all with just the touch of a few buttons.

STORE directly as folder searchable content, capture incoming faxes and create editable documents in a myriad of file formats.

SEARCH easily through every word in your new PDF document library.

SECURE your Intellectual Property (IP). It's valuable so keep it out of harms' way with passwords, encryption and email security.

No more retyping of old documents. RE-RITE® is accurate, efficient and works with free industry standard software such as Adobe® Reader® to keep your documents safe and compatible for years to come.

Toshiba's e-BRIDGE Re-Rite™ **requires only one license per site**, making it a very cost effective entry point to paperless workflow efficiency.

What's more, simple, one touch templates matching your industry type are available.

Scan to WORD®	Scan to EXCEL®	Secure PDF and Email	Store PDF/A in archive	Store as eBook
Send WORD® Email	Search PDF and Email	Store HTML	Batch SEP BARCODE	Scan to PowerPoint



e-BRIDGE Re-Rite™ performs automatic document scanning, optical character recognition, format conversion and document routing to complete workflows with a touch of a single button from your e-STUDIO MFP control panel.

The latest release includes many advances in technology.



PDF A – Ideal for archival purposes, the new PDF A format conforms to internationally agreed protocols and ensures that PDFs scanned today can be opened at any point in the future.



PDF Security – Are you storing documents in Windows folders in an effort to go paperless? Are you concerned that anyone with access to the directories can see your documents? Take advantage of the new enhanced PDF security offered by Toshiba's e-BRIDGE Re-Rite™ to secure the documents. Opening, printing, copying and editing permissions can be permitted or denied.



EMAIL Security – RE-RITE® supports authentication with SMTP servers. Restrict internal security leaks by specifying log-in details when delivering emails.



Scan to 21
editable file
formats



Batch Separation – Do you have large volumes of documents to scan or back scanning jobs waiting to complete? Use separator sheets to feed multiple files through the scanner at once and create separate files. Files may either be separated by bar-coded sheets or based on a fixed number of pages.



METASCAN

MAKING YOUR INFORMATION MEANINGFUL

Taking RE-RITE® to the next level, the **Metascan option** allows users to add a set of keywords to help classify and identify each document scanned.

Rather than routing scanned files to a single folder, Metascan actually uses your keywords to define the folder structure on your network, making it easy to search for any scanned file.

Now you can create your own digital library easily with converted documents neatly archived for you to quickly search and access.

Scanned files route automatically to content searchable folder structures based on your user-selectable Metascan keywords



INPUT

- > Image Auto Rotation
- > Batch split by page interval
- > Batch split by barcode separator
- > BW/Colour
- > MFP scan
- > MFP image files
- > Incoming Fax

OUTPUT

- > File naming with name, date, time, user metadata.
- > To user folders/subfolders
- > Network shares
- > FTP
- > Email

PROCESSING OPTIONS

- > Despeckle
- > Deskew
- > Remove colour
- > Remove distortion
- > Low resolution compensation
- > Optimised for edit
- > Optimised for layout

ADDRESS BOOK

- > MFP
- > LDAP

OUTPUT FORMATS

- > Word (DOC) (DOCX)
- > Excel (XLS) (XLSX)
- > PowerPoint (PPTX)
- > Rich Text Format (RTF)
- > HTML 4.0
- > eBook (ePUB) (FB2)
- > Tabular Data (Unicode and ANSI encoding)
- > Unformatted Text (Unicode and ANSI encoding)
- > Formatted Text (Unicode and ANSI encoding)
- > Comma Separated Value (Unicode and ANSI encoding)
- > PDF Text only
- > PDF Image Substitution Text
- > PDF Image on Text
- > PDF Compressed

PDF SECURITY

- > Owner Password
- > User Password
- > Encryption (40bit) (128bit)

PDF FILE ACCESS RESTRICTIONS

- > Comments
- > Document Assembly
- > Content Copying
- > Printing
- > Form Fields
- > Document Editing
- > Content Extraction
- > High Quality Printing

PDF VERSIONS

- > PDF version 1.3
- > PDF version 1.4
- > PDF version 1.5
- > PDF version 1.6
- > PDF version 1.7
- > PDF version A
- > PDF version A - 1a
- > PDF version A - 1b

Microsoft Windows, Windows NT, and the brand names and other product names of other Microsoft products are trademarks of Microsoft Corporation in the United States and/or other countries.

Acrobat® is a registered trademark of Adobe systems, Inc.

ABBYY and FineReader are registered trade marks of ABBYY Software House.

RE-RITE™ is a registered trademark of Toshiba (Australia) Pty Limited (ABN 19 001 320 421)

All other brands and/or product names are trademarks of their respective owners.

Specifications are subject to change without notification.

Authorised Toshiba Dealer

Toshiba e-BRIDGE Re-Rite™ is a complete, easy-to-use and affordable office automation platform.

Enhance your Toshiba e-STUDIO MFP to automatically convert scanned paper documents into editable and searchable files. Now with Version 8, new features allow you to scan, convert, store and distribute documents securely to streamline office workflows like never before.

It's accurate, efficient and simple to use. Toshiba e-BRIDGE Re-Rite™ your gateway to document imaging workflow.

OCR OUTPUT LANGUAGES

Albanian	Bulgarian	Czech	Danish
Dutch	English	Estonian	Finnish
French	German	Greek	Hungarian
Italian	Latvian	Lithuanian	Macedonian
Maltese	Norwegian	Polish	Portuguese
Romanian	Russian	Serbian	Slovak
Slovenian	Spanish	Swedish	Turkish
Ukrainian			

RECOMMENDED SYSTEM REQUIREMENTS

	Required	Recommended
Processor	Pentium IV 2.66GHz or equivalent	Pentium Dual CPU 1.60GHz (or better)
RAM	256MB	1GB (or more)
Free Disk Space	200MB for software + additional space for data if stored on the same system	200MB for software + additional space for data if stored on the same system
Supported Platforms	e-BRIDGE Re-Rite 8 has been tested on the following Operating Systems: Windows® XP Professional SP3 32-bit Windows Vista Business SP2 32-bit Windows Vista Ultimate SP2 32-bit Windows 7 Professional SP1 32-bit Windows 7 Professional SP1 64-bit Windows 7 Ultimate SP1 64-bit Windows 7 Enterprise 32-bit Windows Server 2003 SBS SP2 32-bit Windows Server 2003 Standard Edition SP2 32-bit Windows Server 2003 Standard Edition R2 SP2 32-bit Windows Server 2003 Enterprise Edition SP2 32-bit Windows Server 2008 Standard Edition SP2 64-bit Windows Server 2008 Enterprise Edition SP2 64-bit MS Hyper-V Guest OS: Windows 7 Enterprise 32-bit Windows Vista Ultimate SP2 32-bit Windows 7 Professional SP1 32-bit Windows 7 Professional SP1 64-bit Windows Server 2003 Standard Edition SP2 32-bit Windows Server 2003 Standard Edition R2 SP2 32-bit Windows Server 2003 Enterprise Edition SP2 32-bit Windows Server 2008 Standard Edition SP2 64-bit Windows Server 2008 Enterprise Edition SP2 64-bit MS Virtual PC: Windows XP Professional SP3 32-bit Windows Server 2003 SBS SP2 32-bit Windows Server 2003 Standard Edition SP2 32-bit Windows Server 2003 Enterprise Edition SP2 32-bit RESTRICTION: MAC address allocation in Virtual Machines should be static for all clients installing e-BRIDGE Re-Rite software.	
Screen Resolution	15" or 17" display at 1024 x 768 pixels	
Web Browser	IE 7, IE 8, Firefox 3.6, Google Chrome 7 & 8	
Network Card	10/100BaseT/X for MFP access	
CD ROM	For installation	
Toshiba Multifunction Device	e-STUDIO MFP with scan feature utilising e-BRIDGE 1, 2, 3 and X architecture. Not all features available with all models. Check with a Toshiba representative for the latest product compatibility.	

A dedicated PC that is available on the network at all times is recommended for hosting the software. This may be a server system.

TOSHIBA
Leading Innovation >>>

Powered by
ABBYY®

Designs and Specifications subject to change without notice.